



Muelle de gas POWERLINE con base reforzada

Variantes de sujeción


2480.007.05000




2480.008.05000³⁾




2480.010.05000.160³⁾




2480.011.05000




2480.011.05000.2




2480.022.05000




2480.044.05000²⁾




2480.044.03.05000²⁾




2480.045.05000²⁾




2480.047.05000²⁾




2480.055.05000



2480.057.05000



2480.064.05000⁴⁾



Nota:

- 2) Atención:
¡La fuerza del muelle tiene que ser absorbida por la superficie de impacto!
- 3) No puede emplearse para conexión combinada.
- 4) Breda de sección cuadrada con valona, con seguro anti-giro, sujeción para conexión combinada.
- 5) Tornillos cilíndricos Allen (recomendado: con cabeza de altura reducida).